

Ethernet system for temperature measurement

16/8/4 channels for thermocouples or RTD, 24-bit




MSX-E3211

16/8/4 differential inputs, 24-bit

For thermocouples or RTD (Pt 100, Pt 1000)

Simultaneous data acquisition up to 8 channels

24 V digital trigger input




Integrated
Ethernet
switch




*Operating temperature



ARM[®]9
Technology



Cascadable, can be
synchronised
in the μ s range



On request:
Compare logic for
synchro trigger signal



on request



DatabaseConnect
see page 112



More information at
www.addi-data.com

Features

- 24 V digital trigger input
- ARM[®]9 32-bit processor
- 64 MB onboard SDRAM for storing data
- Robust standardized metal housing
- Power Save Mode: Reduced power consumption when no acquisition runs

Safety features

- Status LEDs for fast error diagnostics
- Optical isolation
- Input filters

Temperature inputs

- 16/8/4 differential inputs for thermocouples or RTD, 24-bit
- Sampling frequency max. 788 Hz/channel (max. 8/4/2 channels simultaneously)
- Auto gain: Optimal adjustment of the gain to the measuring range
- Integrated cold junction compensation (CJC) for thermocouples
- NTC sensors optional

Interfaces

- Fast 24 V trigger input
- Ethernet switch with 2 ports
- Synchronisation/trigger In/Out
- 24 V supply and cascading


Communication interface

- Web server (configuration and monitoring)
- Command server SOAP for transferring commands
- Data server (TCP/IP or UDP socket) for sending acquisition data
- Event server (TCP/IP socket) for sending system events (Diagnostics such as temperature, short-circuits ...)
- Command server Modbus TCP and Modbus (UDP) for sending commands


Synchronisation/time stamp

Time stamp

Several MSX-E systems can be synchronised with one another in the μ s range through a synchro connection. This allows to start a synchronous data acquisition, to generate trigger events and to synchronise the time on several MSX-E systems. Furthermore, the systems have a time stamp that logs the point in time at which the data was acquired by the system.




The combination of synchronisation and time stamp (TS) allows the clear allocation of signals that were captured by several systems.



Acquisition modes


Auto-refresh mode

In auto-refresh mode, the measurement values are updated automatically after each acquisition. The acquisition is initialised once and the values of the channels are stored in the memory of the MSX-E Ethernet system. The client (e.g. PC, server, PLC, ...) reads the acquired values asynchronously to the acquisition through socket connection, SOAP or Modbus function. Thereby, the new value is read and the old values are overwritten. In addition to the measurement values, the auto-refresh counter can also be read, which allows to sort the measurement values chronologically. The auto-refresh mode can be combined with a hardware or a synchro trigger and also allows the automatic averaging of values.




Sequence mode

In sequence mode, a list of channels is acquired. Thereby, the single measurement rows are stored one after another. The client receives the acquired values asynchronously to the acquisition through a socket connection. In the sequence mode, the measurement values are read in chronological order, this means the oldest values are read first. The acquisition can be effected continuously, with or without delay or in combination with a hardware or synchro trigger.




Acquisition triggered through trigger or synchro input

Example: A measurement process is to be started through an external trigger impulse. For each trigger, 10 sequences are to be acquired. After the acquisition of the 10 sequences they are to be sent to the client.



Reading data from a MSX-E system


MSX-E systems are multi-client capable, this means several clients (e. g. PC, server, PLC, ...) can read the measurement values of one MSX-E system at the same time. For this, each client establishes a socket connection to the data server of the MSX-E system (port 8989). As soon as the measurement values are available on the data server, the MSX-E system transfers them to the clients.



Onboard programming / stand-alone operation

Development mode

With the Development mode of the MSX-E systems you can customise your measurement, control and regulation applications to fit your requirements. The programs run directly on the MSX-E systems, which has two advantages: external PCs are relieved and you can process data freely according to your requirements. This helps you to improve the efficiency of your processes and to secure your investments.



NOTE

With thermocouples, it is only possible to capture the relative temperature between the terminal to which the thermocouple is connected and the welding spot. For this reason, in order to calculate the actual temperature at the measuring point, it is necessary to capture an absolute temperature on a second sensor (PTC). This is called cold junction compensation (CJC) and is included on the MSX-E3211-TC system.

ConfigTools

The **ConfigTools** program allows an easy administration of the MSX-E systems. These are recognised automatically in the network. **ConfigTools** consists of common and specific functions.


In addition, with **ConfigTools**, the complete configuration of a MSX-E system can be saved and transferred to another system of the same type (clone function).

ConfigTools is included in the delivery.

ConfigTools functions for MSX-E3211:


- Change of IP address
- Display of web interface
- Firmware update
- Save/load system configuration
- Save/load channel configuration
- Monitoring the temperature inputs

Very easy use through the „ConfigTools“ program; The MSX-E system is automatically detected in the network.




Monitor function example for temperature inputs


Features




Simplified block diagram



Cascading



ADDI-DATA connection technology





Specifications

Analog inputs

Number of inputs:	16, 8 or 4 differential inputs for thermocouples or RTD 2 outputs for each M12 connector		
Resolution:	24-bit		
Optical isolation:	1000 V		
Throughput:	max. 788 Hz for 1 channel, max. 528 Hz for 2 channels		
Current source:	~200 µA (intern kalibriert)		
Real acquisition frequency:	at	at	Sampling frequency (software programmable)
	1 channel	2 channels	
	2.37 Hz	1.585 Hz	5 Hz
	4.73 Hz	3.154 Hz	10 Hz
	9.37 Hz	6.243 Hz	20 Hz
	18.9 Hz	12.6 Hz	40 Hz
	37.35 Hz	24.89 Hz	80 Hz
	73 Hz	48.65 Hz	160 Hz
	145 Hz	96.8 Hz	320 Hz
	276.4 Hz	184.26 Hz	640 Hz
	407.83 Hz	271.96 Hz	1 kHz
	788 Hz	525.48 Hz	2 kHz

Voltage supply, Ethernet, Trigger, Synchro

The specifications for the voltage supply, Ethernet, Trigger, Synchronisation and Electromagnetic Compatibility apply to all MSX-E systems. See page 31.

System features

Interface:	Ethernet acc. to specification IEEE802.3
Dimensions (mm):	220 x 140 x 50
Weight:	620 g
Degree of protection:	IP 65
Current consumption:	150 mA ± 10 % typ. in idle/power save
Operating temperature:	-40 °C to +85 °C

Connectors for sensors

Analog inputs: 8, 4 or 2 x 8-pin M12 female connector

Ordering information

MSX-E3211

Ethernet system for temperature measurement, 16/8/4 channels for thermocouples or RTD, 24-bit. Incl. technical description and software drivers.

Versions

MSX-E3211-TC-16:	for 16 thermocouples
MSX-E3211-TC-8:	for 8 thermocouples
MSX-E3211-TC-16:	for 4 thermocouples
MSX-E3211-RTD-16:	for 16 RTD
MSX-E3211-RTD-8:	for 8 RTD
MSX-E3211-RTD-4:	for 4 RTD

Connection cables

Voltage supply

CMX-2x: Shielded cable, M12 5-pin female connector/open end, IP 65

CMX-3x: For cascading, shielded cable, M12 5-pin female connector/male connector IP 65

Trigger/Synchro

CMX-4x: Shielded cable, M12 5-pin female connector/open end, IP 65

CMX-5x: For cascading, shielded cable, M12 5-pin female connector/male connector IP 65

Ethernet

CMX-6x: CAT5E cable, M12 D-coded male connector/RJ45 connector

CMX-7x: For cascading: CAT5E cable, 2 x M12 D-coded male connector

Options

S7 Modbus TCP Client Library for S7: Easy use of the Ethernet systems MSX-E with PLCs

MSX-E 5V-Trigger: Level change of the trigger inputs and outputs to 5 V

MSX-E-Filter-20Hz: 20 Hz input filter

MSX-E-NTC-100µA: for NTC sensors with 0-20 kΩ

MSX-E-NTC-50µA: for NTC sensors with 0-40 kΩ

MX-Rail (Please specify when ordering!),

MX-Screw, PCMX-1x